



Product Specification

Product Name	BK-01
ID	
selling points	<ol style="list-style-type: none"> 1、 45000 times / second ultrasonic high-frequency vibration, 360-degree cleaning all-round cleaning 2、 four UVC+UVA ultraviolet lamps, 99.99% strong sterilization 3、 SUS304 stainless steel sink + food-grade antimicrobial material , safe and secure 4、 a key to the 5-minute sterilization + cleaning, convenient and simple 5、 the volume of sound when running down to 60 decibels, mute and non-intrusive 6、 the appearance of the fashionable sense of technology
Working Principle	<p>The use of "piezoelectric ceramic sheet" ultrasonic generator, 45,000 times per second high-frequency vibration, water in the ultrasonic effect of cavitation effect separates out countless invisible tiny bubbles, small bubbles in the ultrasonic acoustic pressure under the action of rapid expansion and ultimately "explosion ", resulting in close to 1,000 atmospheric pressure of the instantaneous impact of the dirt on the surface of the object is constantly flushed, so that the surface of the dust, bacteria, oil to achieve emulsification, stripping, cleaning up to the micron level of the crevice blind spot. (Vibration frequency directly determines the power of the explosion, ultrasonic explosion formed by the strength of the impact force directly determines the cleaning intensity. 45000Hz high-frequency vibration can bring amazing cleaning effect at the same time will not cause damage to the object.)</p>
Areas of application	<p>Dentures, braces, razor blades, jewelry, watch bracelets, makeup brushes, toothbrushes, manicure tools, printer ink cartridges, pens, stamps, coins and other items</p>
color	White/Black
Product Size	∅116.00mm*118.00mm
Package Size	120.00x120.00x135.00mm
replacement (parts)	Host *1+ Adapter *1+ Instruction manual *1



Specification	
Ultrasonic frequency	45KHz
Ultrasonic power	24W
Rated voltage	12V
Tank Capacity	180mL
operating cycle	5min/session
net weight	317g
gross weight	483g
Outer box size	480.00x480.00x280.00mm(32 units/box)
patents	Appearance Patent
Certification	CE, FCC, EPA
Caution	The whole machine is not waterproof, it is strictly prohibited to immerse the body in any liquid; no water is strictly prohibited to open the machine, so as not to damage the machine; ultrasonic work for a long time will produce heat, in order to avoid high water temperature damage to the cleaning items, it is recommended to rest for 10 minutes after the use of 2 ~ 3 times or replace the room temperature water and then clean; not recommended for cleaning silver (silver oxidation is easy to ultrasonic cleaning of the oxidized layer of the cleaning effect is not obvious); is strictly prohibited to wash the inlaid styles of Jewelry.